



MaxiLED Fitting - Wiring Options

(1 x MaxiLED string) (5 x MaxiLED string)

Multiple Strands 1 to 5 (10xGU10 per Strand)



KEY

Symbol	Description		
	End of line resistor		
	MaxiLED GU10 Retro-Fit		
	Transformer		
Rev	Date	Description	By
2.0	30/8/18	MaxiLED Single and Multiple wiring	CL

Project Title: MaxiLED fitting wiring Single and Multiple strings			
Scale @: NOT TO SCALE			
Drawing Title:			
Drawn CL	Checked AH	Date 30 Aug 2018	Issue Date
Drawing Number: 2.0			Revision: 2.0